

Connections to other Labs

AtomLab - ResLab

BNC

Cable	Application	Informations
BNC 1	Beat with comb	
BNC 2	Photodiode behind cavity	
BNC 3	CCD behind cavity R1	
BNC 4	Photodiode behind fiber	~ 15 mW
BNC 5	External frequency	
BNC 6	External Reset	
LAN-cable	PTB	colour: red

Fiber

GPS / Uni top

Qport - ResLab

From:
<https://iqwiki.iqo.uni-hannover.de/> - IQwiki

Permanent link:
<https://iqwiki.iqo.uni-hannover.de/doku.php?id=groups:mg:connections&rev=1472806058>

Last update: **2016/09/02 08:47**

