

457 nm-Laser (Wutz)

Operation Values

To Do! Picture!



Edit any other values!

Lasersystem - Typical power values

The system was build by ... and is described in his

914 nm-Laser

- Outputpower after TA: ~ 490 mW

457 nm-SHG

- Operation outputpower: ~ 130 mW
 - Max outpupower: 200 W
- Power for photodiode: ~ ... mW

AOM's

- Power infront the AOM in ... order: ... mW
- Power behind the AOM: ... mW (efficiency ~ 50 %)

Fibers

Wutz

- Infront fiber: ...
- After fiber: ... [efficiency ~ ... %]

Spectroscopy

- Infront fiber: ...

- After fiber: ... [efficiency ~ ... %]

Sisyphus

- Infront fiber: ...
- After fiber: ... [efficiency ~ ... %]

Wavemeter

- Infront fiber: ...
- After fiber: ... [efficiency ~ ... %]

Wutz-resonator

From:
<https://iqwiki.iqo.uni-hannover.de/> - IQwiki

Permanent link:
<https://iqwiki.iqo.uni-hannover.de/doku.php?id=groups:mg:experiment:laser:457nmlaser&rev=1440078531>

Last update: **2015/08/20 13:48**

