

457 nm-Laser (Wutz)

Operation Values

To Do! Picture!



Edit any other values!

Lasersystem - Typical power values

The system was build by ... and is described in his

914 nm-Laser

- Outputpower after TA: ~ 490 mW

457 nm-SHG

- Operation outputpower: ~ 130 mW
 - Max outpupower: 200 W
- Power for photodiode: ~ ... mW

AOM's

Double pass AOM (Wutz)

- Power infront the AOM in 1. order: ... mW
- Power behind the AOM: ... mW (efficiency ~ ... %)

AOM 1 (Spectroscopy)

- Power infront the AOM in 1. order: ... mW
- Power behind the AOM: ... mW (efficiency ~ ... %)

AOM 2 (Sisyphus)

- Power infront the AOM in 1. order: ... mW

- Power behind the AOM: ... mW (efficiency ~ ... %)

Fibers

Wutz

- Infront fiber: ...
- After fiber: ... [efficiency ~ ... %]

Spectroscopy

- Infront fiber: ...
- After fiber: ... [efficiency ~ ... %]

Sisyphus

- Infront fiber: ...
- After fiber: ... [efficiency ~ ... %]

Wavemeter

- Infront fiber: ...
- After fiber: ... [efficiency ~ ... %]

Wutz-resonator

- After cube: ... mW
- Infront aperture: ~ 350 mW

From:
<https://iqwiki.iqo.uni-hannover.de/> - IQwiki

Permanent link:
<https://iqwiki.iqo.uni-hannover.de/doku.php?id=groups:mg:experiment:laser:457nmlaser&rev=1440078967>

Last update: 2015/08/20 13:56

